## Thomas&Betts



## Molded Case Circuit Breakers T&B Catalog Number:

<b>UPC Number:</b>
Status:
Description:

A1A015TW 80432554880 Active

3 pole, 15 amps rated at 240V AC and 250V DC, fixed trip point molded case circuit breaker, with a thermal magnetic trip device and 10kA at 240V AC and 5kA at 250V DC interrupt current rating **Features** 

	Smaller size with full protection
	Fixed trip point
	Front mounted terminals
Application	
	For panelboards with 15A - 100A capacity
	Branch circuit protection where small low cost, fixed
	trip point breakers are required
General	
Тгір Туре	Thermal Magnetic
Number of Poles	3
Series	A1A
Approvals	
UL Class	UL 489
Dimension Information	
H x W x D (inches)	5.91 x 3.00 x 2.36
Specifications	
Rated Current (Amps)	15
Rated Voltage AC	240
Rated Voltage DC	250
Interrupt Rating	10kA at 240V AC and 5kA at 250V DC
Packaging	
Package in Units	1
T&B Sold in UOM	Each
T&B Weight Per UOM	1.8 lbs. Each

## For further technical assistance, please contact us...

T&B Technical Support MS 3B-50 8155 T&B Blvd. Memphis, TN 38125 Hours: 7AM - 6PM CDT Monday-Friday Phone: (888) 862-3289 Fax: (901) 252-1321 Email:techsupport@thb.com

Thomas & Betts - USA 8155 T&B Blvd. Memphis, TN 38125 www.tnb.com