

**Molded Case Circuit Breakers****T&B Catalog Number:**

A2N125TW-2

UPC Number:

80432557903

Status:

Active

Description:

2 pole, 125 amps rated at 240V AC and 250V DC, fixed trip point molded case circuit breaker, with a thermal magnetic trip device and 25kA at 240V AC/DC interrupt current rating

Features

Smaller size with full protection

Fixed trip point

Front mounted terminals

Application

For panelboards with 125A - 250A capacity

Branch circuit protection where small low cost, fixed trip point breakers are required

General

Trip Type Thermal Magnetic

Number of Poles 2

Series A2N

Approvals

UL Class UL 489

Dimension Information

H x W x D (inches) 5.91 x 2.76 x 2.36

Specifications

Rated Current (Amps) 125

Rated Voltage AC 240

Rated Voltage DC 250

Interrupt Rating 25kA at 240V AC/DC

Packaging

Package in Units 1

T&B Sold in UOM Each

T&B Weight Per UOM 2.2 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com