



Project: Marathon-International

Location: Cairo, Egypt

Marathon Electrical

Molded Case Circuit Breakers

T&B Catalog Number:

T5S400TW

UPC Number:

66201926453

Status:

Active

Description:

3 pole, 400 amps rated at 600V AC/DC, Tmax molded case circuit breaker with a thermal magnetic trip device and 35kA at 480V AC interrupt current rating

Features

Short circuit protection is provided by an adjustable magnetic trip unit

Advanced contact design and arcing chambers provide the latest in fault current protection

Adjustable trip point adjustable from 2000 to 4000A

Double insulation - allows UL Listed field installation of internal accessories

Application

For power distribution applications

Can be installed in either the horizontal or vertical planes

Suitable for reverse feed applications

General

Trip Type	Thermal Magnetic
Number of Poles	3
Series	T5

Approvals

UL Class	UL 489
----------	--------

Dimension Information

H x W x D (inches)	8.07 x 5.51 x 4.07
--------------------	--------------------

Specifications

Rated Current (Amps)	400
Rated Voltage AC	600
Rated Voltage DC	600
Interrupt Rating	35kA at 480V AC

Packaging

Package in Units	1
T&B Sold in UOM	Each
T&B Weight Per UOM	10.52 lbs. Each

Certifications



File Nbr:
UL 489

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com