

**IEC****T&B Catalog Number:**

S803S-K125

UPC Number:

80432518727

Status:

Active

Description:

3 pole, 125 amps rated at 690 VAC, IEC series high performance circuit breaker with thermal-magnetic trip device, K trip curve, and 50kA interrupt current rating

Features

Fast breaking time
Finger safe terminals
Multi-function terminals
Ring-tongue compatible
IEC current limiting

Application

Designed for the higher inrush currents during system start of inductive loads: as in motor and transformer applications

General

Mounting Method	DIN rail
Trip Type	Thermal-magnetic
Number of Poles	3
Series	S800S-K
Terminal Type	Screw

Approvals

UL Class	IEC Only
----------	----------

Dimension Information

H x W x D (inches)	3.74 x 3.13 x 3.48
H x W x D (mm)	95 x 79.5 x 88.5

Specifications

Rated Current (Amps)	125
Rated Voltage AC	690
Interrupt Rating (kA)	50
Trip Curve	K

Packaging

Package in Units	1
T&B Sold in UOM	Each
T&B Weight Per UOM	1.66 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com