

**Dynamic Braking / DC Drive
T&B Catalog Number:****UPC Number:**

EHDB220C-PL

Status:

66201946455

Description:

Active

3 pole, 2 NO and 1 NC, plus 1 NO and 1 NC auxiliary contacts, 220 amp, DC drive, dynamic braking contactor, with a 110V DC coil

Features

Double-break contacts with magnetic arc chutes
Elevator service rated

Standards

cULus

Application

For use with solid state DC adjustable speed drive systems

General

Series	EHDB
Poles	2 NO and 1 NC
Coil Type	DC
Auxiliary Contacts	1 NO and 1 NC

Dimension Information

H x W x D (inches)	7.79 x 5.83 x 6.65
--------------------	--------------------

Specifications

Coil Voltage	110V DC
DC Continuous Current (A)	220
DC Power Pole Make/Break Voltage (V)	600
DC Power Pole Make/Break Current (C)	333
DC Dynamic Braking Pole Make Voltage (V)	600
DC Dynamic Braking Pole Make Current (A)	450
DC Dynamic Braking Pole Break Voltage (V)	300
DC Dynamic Braking Pole Break Current (A)	285

Packaging

Package in Units	1
T&B Sold in UOM	Each
T&B Weight Per UOM	10.84 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com