

**Railway Applications**
T&B Catalog Number:

A263010RT-84

UPC Number:

66201986103

Status:

Active

Description:

40 amp AC controlled 3 pole ring tongue contactor with a 110-120V AC coil and 1 NO auxiliary contact

Features

Wide temperature range of -40 DEG C to +70 DEG C

Shock and vibration withstand

Standards

IEC

Application

For use in lighting, heating, braking, air conditioning, ventilation and door control in railway rolling stock applications

General

Series A-line

Terminal Type Ring tongue

Poles 3

Coil Type AC

Auxiliary Contacts 1 NO

Dimension Information

H x W x D (inches) 3.54 x 2.13 x 3.69

Specifications

3dmodel Available on Website

Coil Voltage 110-120V AC

UL Maximum Motor Switching Amps 28

Packaging

T&B Inner Pack 1

Package in Units 24

T&B Sold in UOM Each

T&B Weight Per UOM 1.3 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com