

**Control Circuit Transformers****T&B Catalog Number:**

T6050PS1

UPC Number:

66201958617

Status:

Active

Description:

50 VA rating 4 terminal transformer with 0.43 output amps with a primary fuse block and a secondary fuse clip

Features

Epoxy encapsulated coils up through 750VA

Epoxy resin impregnated coils 1 kVA to 5 kVA

Laminations of high quality silicon steel

Minimum core loss

Copper magnet wire providing the highest quality and efficient operation

Molded-in terminals

93 degree C rise, 130 degree C insulation system

IP 20 Touch safe covers available as an option

Standards

UL File # E175311; CSA File #LR27533

Application

Provides stepped down voltages for machine tool control devices and industrial control panels

Dimension Information

H x W x D (inches) 2.99 x 2.99 x 3.94

H x W x D (mm) 76 x 76 x 100

Specifications

Output Current (Amps) 0.43

Packaging

Package in Units 1

T&B Sold in UOM Each

T&B Weight Per UOM 2.98 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com