

## Control Circuit Transformers T&B Catalog Number:

X4750PS1

**UPC Number:** 80432536750

Status: Active

**Description:** 

750 VA rating 6 terminal transformer with 6.52 output amps with a primary fuse block and a secondary fuse clip

Features	- 1
i eatures	
	Epoxy encapsulated coils up through 750VA
	Epoxy resin impregnated coils 1 kVA to 5 kVA
	Laminations of high quality silicon steel
	Minimum core loss
	Copper magnet wire providing the highest quality and efficient operation
	Molded-in terminals
	80 degree C rise, 130 degree C insulation system
	IP 20 Touch safe covers available as an option
Standards	
	UL File # E175311; CSA File #LR27533
Application	
	Provides stepped down voltages for machine tool control devices and industrial control panels
Dimension Information	control devices and industrial control pariets
H x W x D (inches)	7.63 x 5.25 x 6.00
H x W x D (mm)	193 x 133 x 151
Specifications	
Output Current (Amps)	6.52
Packaging	
Package in Units	1
T&B Sold in UOM	Each
T&B Weight Per UOM	25.43 lbs. Each

For further technical assistance, please contact us...

T&B Technical Support MS 3B-50 8155 T&B Blvd. Memphis, TN 38125 Hours: 7AM - 6PM CDT Monday-Friday Phone: (888) 862-3289 Fax: (901) 252-1321 Email:techsupport@tnb.com

Thomas & Betts - USA 8155 T&B Blvd. Memphis, TN 38125 www.tnb.com