

Control Circuit Transformers T&B Catalog Number:

X4500PSF1

UPC Number: 80432536753 **Status:** Active

Status: Description:

500 VA rating 6 terminal transformer with 20.84/4.35 output amps with a primary fuse block and a secondary fuse clip

. ,	, ,
Features	
	Epoxy encapsulated coils up through 750VA
	. ,
	Epoxy resin impregnated coils 1 kVA to 5 kVA
	Laminations of high quality silicon steel
	Minimum core loss
	Copper magnet wire providing the highest quality
	and efficient operation
	Molded-in terminals
	88 degree C rise, 130 degree C insulation system
	IP 20 Touch safe covers available as an option
Standards	
	UL File # E175311; CSA File #LR27533
Application	
	Provides stepped down voltages for machine tool
	control devices and industrial control panels
Dimension Information	
H x W x D (inches)	6.10 x 5.24 x 5.94
H x W x D (mm)	155 x 133 x 151
Specifications	
Output Current (Amps)	20.84/4.35
Packaging	
Package in Units	1
T&B Sold in UOM	Each
T&B Weight Per UOM	22.27 lbs. Each

For further technical assistance, please contact us...

T&B Technical Support MS 3B-50 8155 T&B Blvd. Memphis, TN 38125 Hours: 7AM - 6PM CDT Monday-Friday Phone: (888) 862-3289 Fax: (901) 252-1321 Email:techsupport@tnb.com

Thomas & Betts - USA 8155 T&B Blvd. Memphis, TN 38125 www.tnb.com