

## **Control Circuit Transformers T&B Catalog Number:**

X4100PSF1

**UPC Number:** 80432536746 Active

Status:

**Description:** 

100 VA rating 4 terminal transformer with 4.17/0.87 output amps with a primary fuse block and a secondary fuse clip

Features	
	5 J. J. J. J. 750/A
	Epoxy encapsulated coils up through 750VA
	Epoxy resin impregnated coils 1 kVA to 5 kVA
	Laminations of high quality silicon steel
	Minimum core loss
	Copper magnet wire providing the highest quality
	and efficient operation
	Molded-in terminals
	83 degree C rise, 130 degree C insulation system
	IP 20 Touch safe covers available as an option
Standards	
	III E'' " E475044 OOA E'' "I DO7500
	UL File # E175311; CSA File #LR27533
Application	
	Provides stepped down voltages for machine tool
	control devices and industrial control panels
Dimension Information	control devices and industrial control pariets
Difficusion information	
H x W x D (inches)	4.53 x 3.74 x 4.65
H x W x D (mm)	115 x 95 x 118
Specifications	
Output Current (Amps)	4.17/0.87
Packaging	
Package in Units	1
T&B Sold in UOM	Each
T&B Weight Per UOM	6.79 lbs. Each

## For further technical assistance, please contact us...

**T&B Technical Support** MS 3B-50 8155 T&B Blvd. Memphis, TN 38125

Hours: 7AM - 6PM CDT Monday-Friday Phone: (888) 862-3289 Fax: (901) 252-1321 Email:techsupport@tnb.com

Thomas & Betts - USA 8155 T&B Blvd. Memphis, TN 38125 www.tnb.com