

**Capacitive Switching
T&B Catalog Number:**

UA75-30-00-84

UPC Number:

66201970672

Status:

Active

Description:

3 pole, 70 amp, general purpose rated, UA 75 capacitive switching contactor with a 110-120V AC rated coil

Features

The UA to RA contactors are fitted with a special front-mounted block, which ensures the serial insertion of 3 damping resistors into the circuit to limit the current peak on energization of the capacitor bank

Connection also ensures capacitor precharging in order to limit the second current peak occurring upon making of the main poles

The insertion of resistors allows to dampen the highest current peak of the capacitor when switching on, whatever its level

Standards

UL

Application

For capacitive switching applications up to 130 kVar

General

Series	UA
Poles	3
Coil Type	AC

Specifications

3dmodel	Available on Website
Coil Voltage	110-120V AC

Packaging

T&B Inner Pack	1
Package in Units	20
T&B Sold in UOM	Each
T&B Weight Per UOM	2.49 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com