



Lighting

T&B Catalog Number:

A16-120L-00-84

UPC Number:

66201968517

Status:

Active

Description:

12 pole, 30 ballast amp, 30 incandescent amp, electrically held open type lighting contactor with 110V AC, 120V AC and 110V DC coil and no auxiliary contacts

Features

Compact, space saving design

Panel mounting with screws or fast, snap-on DIN rail mounting

Silver alloy double break contact design

Snap-on front mounted accessories include mechanical latch, pneumatic timer, and 1 and 4 pole auxiliary contact

Contactors ensure positive safety between their auxiliary contact blocks

Easy coil change

Standards

UL, CSA

Application

Primarily for controlling a variety of lighting loads

General

Series A-line

Terminal Type Box Lug

Poles 12

Coil Type AC/DC

Dimension Information

H x W x D (inches) 11 x 6 x 5

Specifications

Coil Voltage 110V AC/DC

Amps 30

Ballast Rating (A) 30

Incandescent Rating (A) 20

Packaging

Package in Units 1

T&B Sold in UOM Each

T&B Weight Per UOM 5 lbs. Each

Notes

Additional auxiliary contacts available

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com