

**Open Switches**
T&B Catalog Number:

OT200U12
66201919176
Active

UPC Number:
Status:
Description:

3 pole, 200 amps rated at 600 VAC, UL 98, open non-fusible disconnect switch

Features

Quick make, quick brake mechanism
Extremely compact size
Finger-proof construction with no hazardous exposed parts

Application

Suitable for use as motor disconnects or industrial control panel disconnects on service entrance equipment, panelboards, switchboards, industrial control equipment, motor control centers, etc.
Motor feeder applications and motor feeder short circuit and ground fault protection

General

Number of Poles 3
Series Non-fusible

Approvals

UL Class UL 98

Dimension Information

H x W x D (inches) 6.69 x 6.67 x 3.3

Specifications

Rated Current (Amps) 200
Rated Voltage AC 600

Packaging

Package in Units 1
T&B Sold in UOM Each
T&B Weight Per UOM 3.57 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com