

**Open Switches**
T&B Catalog Number:

OES600J3-FC

UPC Number:

66201907416

Status:

Active

Description:

3 pole, 600 amps rated at 600 VAC, UL 98, flange operated open fusible disconnect switch for use with J fuse type

Features

Fuses are totally isolated in the 'OFF' position, reducing the risk of shock to authorized personnel

Basic construction provides flexibility and high performance in an extremely compact size

Quick make, quick brake mechanism

Finger proof construction plus terminal shrouds reduce the risk of touching live parts

Application

Suitable for use as motor disconnects or industrial control panel disconnects on service entrance equipment, panelboards, switchboards, industrial control equipment, motor control centers, etc.

Motor feeder applications and motor feeder short circuit and ground fault protection

General

UL Fuse Type	J
Number of Poles	3
Series	Fusible

Approvals

UL Class	UL 98
----------	-------

Specifications

Rated Current (Amps)	600
Rated Voltage AC	600

Packaging

Package in Units	1
T&B Sold in UOM	Each
T&B Weight Per UOM	50.79 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com