



SNA Terminal Blocks

T&B Catalog Number:

UPC Number:

019000120

Status:

66201996403

Description:

Active

Gray, power terminal block bistable foot and base mounting, 27 mm spacing, and 125 Amp rated UL current, accepts 1 AWG max. wire size

Features

	Bistable foot and base mounting
	Self-locking clamp design prevents screw loosening
	Funneled side entry for up to two ferruled or non-ferruled solid or stranded wires
	Touch-safe IP20 protection
	High quality steel offers a very high over-torque resistance
	Compensates for the flattening of copper under contact pressure
	Clamp is protected from harsh environments by a zinc bichromate surface treatment

Application

	For use with applications ranging from standard distribution and control panels, to specialized applications in key industries such as traction, energy, maritime, explosive atmospheres, material handling, etc.
--	---

General

Style	Power Block
Color	Gray
Mounting	DIN 3
Series	D 35/27.FF
UL Wire Range (AWG)	1 max.
Rated IEC Wire Range (Solid) (mm ²)	35
Rated CSA Wire Size (AWG)	1 max.

Dimension Information

L x W x H (mm)	113 x 27 x 59
Spacing (mm)	27
L x W x H (in)	4.45 x 1.06 x 2.32
Spacing (inches)	1.063

Specifications

UL Current (Amps)	125
UL Voltage (VAC)	600
Rated UL Wire Size (AWG)	1 max.
IEC Voltage (VAC)	1000
IEC Current (Amps)	125
CSA Voltage (VAC)	600
CSA Current (Amps)	125

Packaging

T&B Order Multiple	10
T&B Inner Pack	10
Package in Units	80
T&B Sold in UOM	Each

T&B Weight Per UOM

24.5 lbs. per 100

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com