

**SNA Terminal Blocks**
T&B Catalog Number:012568615
66201906054
Active**UPC Number:**
Status:
Description:

Blue/Orange heavy duty switch terminal blocks with blade UL rated 10 Amps with a screw clamp connection that accepts 22 - 10 AWG wire range

Features

Includes IP20 protection

Application

For use with applications ranging from standard distribution and control panels, to specialized applications in key industries such as traction, energy, maritime, explosive atmospheres, material handling, etc.

General

T&B Replacement Catalog Number	012543814
Style	Feed Through
Color	Blue and Orange
Mounting	DIN 1-3
Series	M4/6.SNB
Connection Technology	Screw Clamp
UL Wire Range (AWG)	22-10

Dimension Information

Spacing (mm)	6
Spacing (inches)	0.238

Specifications

UL Current (Amps)	10
UL Voltage (VAC)	300
Rated UL Wire Size (AWG)	10

Packaging

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	750
T&B Sold in UOM	Each
T&B Weight Per UOM	0.02 lbs. Each

Certifications

Approvals	UL
-----------	----

For further technical assistance, please contact us...Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.comT&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com