



SNA Terminal Blocks

T&B Catalog Number:

011565907

UPC Number:

66201995746

Status:

Active

Description:

Gray and blue, fuse holder block with 8 mm spacing, 10 Amp rated UL current with screw clamp connection that accepts 22-12 AWG UL wire range

Features

- Self-locking clamp design prevents screw loosening
- Quick fuse installation and replacement
- Touch-safe IP20 protection
- High quality steel offers a very high over-torque resistance
- Compensates for the flattening of copper under contact pressure
- Clamp is protected from harsh environments by a zinc bichromate surface treatment

Application

For use with applications ranging from standard distribution and control panels, to specialized applications in key industries such as traction, energy, maritime, explosive atmospheres, material handling, etc.

General

| | |
|---|---------------|
| Style | Fuse Holder |
| Color | Gray and Blue |
| Mounting | DIN 1-3 |
| Series | M 4/8.SN |
| Connection Technology | Screw Clamp |
| UL Wire Range (AWG) | 22-12 |
| Rated IEC Wire Range (Solid) (mm ²) | 4 |
| Rated CSA Wire Size (AWG) | 12 |

Dimension Information

| | |
|------------------|-------|
| Spacing (mm) | 8 |
| Spacing (inches) | 0.315 |

Specifications

| | |
|--------------------------|-----|
| UL Current (Amps) | 10 |
| UL Voltage (VAC) | 600 |
| Rated UL Wire Size (AWG) | 12 |
| IEC Voltage (VAC) | 630 |
| IEC Current (Amps) | 6.3 |
| CSA Voltage (VAC) | 250 |
| CSA Current (Amps) | 10 |

Packaging

| | |
|--------------------|-----------------|
| T&B Order Multiple | 50 |
| T&B Inner Pack | 50 |
| Package in Units | 450 |
| T&B Sold in UOM | Each |
| T&B Weight Per UOM | 40 lbs. per 100 |

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com