



## SNA Terminal Blocks

### T&B Catalog Number:

**UPC Number:**

029016100

**Status:**

66201997027

**Description:**

Active

Gray double deck terminal block with 5mm spacing and 20 amp UL rated current with spring clamp connection

### Features

Touch-safe IP20 protection

### Application

For use with applications ranging from standard distribution and control panels, to specialized applications in key industries such as traction, energy, maritime, explosive atmospheres, material handling, etc.

### General

Style	Double Deck Feed Through
Color	Gray
Mounting	DIN 3
Series	D 2.5/5.D2.L
Connection Technology	Spring Clamp
UL Wire Range (AWG)	26-12
Rated IEC Wire Range (Solid) (mm <sup>2</sup> )	2.5
Rated CSA Wire Size (AWG)	12

### Dimension Information

Spacing (mm)	5
L x W x H (in)	3.74 x .198 x 2.22
Spacing (inches)	0.198

### Specifications

UL Current (Amps)	20
UL Voltage (VAC)	300
Rated UL Wire Size (AWG)	12
IEC Voltage (VAC)	500
IEC Current (Amps)	20

### Packaging

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	450
T&B Sold in UOM	Each
T&B Weight Per UOM	3 lbs. per 100

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com