



## SNA Terminal Blocks

### T&B Catalog Number:

**UPC Number:**  
**Status:**  
**Description:**

010512416  
66201995370  
Active

Yellow, feed through terminal block with 16 mm spacing, 150 Amp rated UL current with screw clamp connection that accepts 10-0 AWG UL wire range

### Features

- Self-locking clamp design prevents screw loosening
- Funneled side entry for up to two ferruled or non-ferruled solid or stranded wires
- Touch-safe IP20 protection
- High quality steel offers a very high over-torque resistance
- Compensates for the flattening of copper under contact pressure
- Clamp is protected from harsh environments by a zinc bichromate surface treatment

### Application

For use with applications ranging from standard distribution and control panels, to specialized applications in key industries such as traction, energy, maritime, explosive atmospheres, material handling, etc.

### General

Style	Feed Through
Color	Yellow
Mounting	DIN 1-3
Series	M 35/16
Connection Technology	Screw Clamp
UL Wire Range (AWG)	10-0
Rated IEC Wire Range (Solid) (mm <sup>2</sup> )	35

### Dimension Information

L x W x H (mm)	49 x 16 x 59
Spacing (mm)	16
L x W x H (in)	1.93 x 0.630 x 2.32
Spacing (inches)	0.63

### Specifications

UL Current (Amps)	150
UL Voltage (VAC)	600
IEC Voltage (VAC)	800
IEC Current (Amps)	125
CSA Voltage (VAC)	600
CSA Current (Amps)	140

### Packaging

T&B Order Multiple	20
T&B Inner Pack	20
Package in Units	300
T&B Sold in UOM	Each
T&B Weight Per UOM	10 lbs. per 100

## Certifications

Approvals

UL, IEC, CSA

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)