



Ground Fault Equipment Protectors T&B Catalog Number:

UPC Number:

F202AC-25/0.1

Status:

66201921179

Description:

Active

2 pole, 25 amps rated at 240 VAC, UL 1053 ground fault equipment protector, AC type, 100mA trip sensitivity

Features

Suitable for protection of equipment from AC earth leakage current

UL File No. E244046

Application

Provides ground fault protection (earth leakage) for several branch, miniature circuit breakers

Can be used as a main device providing ground fault protection against earth leakage for several MCB branch devices

General

Mounting Method

DIN rail

Number of Poles

2

Series

F200AC

Terminal Type

Screw

Approvals

UL Class

UL 1053

Dimension Information

H x W x D (inches)

3.5 x 2.7 x 1.4

H x W x D (mm)

88 x 69 x 35

Specifications

Rated Current (Amps)

25

Rated Voltage AC

480

Sensitivity (mA)

0.01, 0.03, 0.1, 0.3, 0.5

Frequency Rating (Hz)

50 - 60

Packaging

T&B Inner Pack

1

Package in Units

6

T&B Sold in UOM

Each

T&B Weight Per UOM

47.5 lbs. per 100

Application Support

Product Brochure

Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com