



Ground Fault Equipment Protectors T&B Catalog Number:

UPC Number: F204AC-25/0.5
Status: 66201923030
Description: Active

4 pole, 25 amps rated at 480 VAC, UL 1053 ground fault equipment protector, AC type, 500mA trip sensitivity

Features

Suitable for protection of equipment from AC earth leakage current

UL File No. E244046

Application

Provides ground fault protection (earth leakage) for several branch, miniature circuit breakers

Can be used as a main device providing ground fault protection against earth leakage for several MCB branch devices

General

Mounting Method	DIN rail
Number of Poles	4
Series	F200AC
Terminal Type	Screw

Approvals

UL Class	UL 1053
----------	---------

Dimension Information

H x W x D (inches)	3.5 x 2.7 x 2.8
H x W x D (mm)	88 x 69 x 70

Specifications

Rated Current (Amps)	25
Rated Voltage AC	480
Sensitivity (mA)	0.01, 0.03, 0.1, 0.3, 0.5
Frequency Rating (Hz)	50 - 60

Packaging

Package in Units	1
T&B Sold in UOM	Each
T&B Weight Per UOM	1.48 lbs. Each

Application Support

Product Brochure	Available on Website
------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com