

**Manual Transfer Switch**
T&B Catalog Number:

OT25F3C
80432541544
Active

UPC Number:**Status:****Description:**

3 pole, 30 amps rated at 600 VAC, UL 508, double throw open non-fusible disconnect switch

Features

Quick make, quick brake mechanism

Extremely compact size

Finger-proof construction with no hazardous exposed parts

Application

Industrial control panel disconnects

For use in motor controller and motor overload protection applications

Can be used as an OSHA lockout/tagout disconnect

General

Style Double Throw

Number of Poles 3

Series Non-fusible

Approvals

UL Class UL 508

Dimension Information

H x W x D (inches) 2.36 x 2.76 x 2.68

Specifications

Rated Current (Amps) 30

Rated Voltage AC 600

Packaging

Package in Units 1

T&B Sold in UOM Each

T&B Weight Per UOM 55.5 lbs. per 100

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com