Thomas@Betts



Manual Transfer Switch T&B Catalog Number:

OT40F3C

UPC Number: 80432541555 Status: Active

Status: Description:

3 pole, 40 amps rated at 600 VAC, UL 508, double throw open non-fusible

disconnect switch	·
Features	
	Quick make, quick brake mechanism
	Extremely compact size
	Finger-proof construction with no hazardous exposed parts
Application	
	Industrial control panel disconnects
	For use in motor controller and motor overload pro- tection applications
	Can be used as an OSHA lockout/tagout disconnect
General	
Style	Double Throw
Number of Poles	3
Series	Non-fusible
Approvals	
UL Class	UL 508
Dimension Information	
H x W x D (inches)	2.36 x 2.76 x 2.68
Specifications	
Rated Current (Amps)	40
Rated Voltage AC	600
Packaging	
Package in Units	1
T&B Sold in UOM	Each
T&B Weight Per UOM	55.5 lbs. per 100

For further technical assistance, please contact us...

T&B Technical Support MS 3B-50 8155 T&B Blvd. Memphis, TN 38125 Hours: 7AM - 6PM CDT Monday-Friday Phone: (888) 862-3289 Fax: (901) 252-1321 Email:techsupport@tnb.com

Thomas & Betts - USA 8155 T&B Blvd. Memphis, TN 38125 www.tnb.com