



Liquidtight Flexible Cord & Cable Fittings

T&B Catalog Number:

2558

UPC Number:

78621002558

Status:

Active

Description:

1-1/4 in. straight die cast zinc liquidtight strain relief cord connector, cord range-.880-1.065.

Application

Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC 501-4(b).

Meets Coast Guard CG293

General

Material Die Cast Zinc

Dimension Information

Hub Size (inches)	1 1/4
Dimension A (inches)	2 3/32
Dimension B (inches)	2 5/32
Dimension C (inches)	13/16
Cord Range (inches)	.880-1.065
Throat Diameter (inches)	1 17/64

Specifications

3dmodel	Available on Website
Temperature Rating	105 C

Packaging

T&B Inner Pack	5
Package in Units	50
T&B Sold in UOM	Each
T&B Weight Per UOM	57.63 lbs. per 100

Application Support

Product Overview	Available on Website
Specifications	Available on Website
Portable Cord Selection Table	Available on Website

Notes

Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC 501-4(b).

Certifications

RoHS Compliance Yes

Certifications



File Nbr:
E 13938

For further technical assistance, please contact us...

8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com