

2559

## ***T&B Industrial Fitting***

Liquidtight strain relief fitting with a hub size of 1-1/4 in.



### General

Type:	Flexible Cord and Cable Fittings
T&B UPC:	78621002559
T&B Status:	M
Special Features:	UL Listed as liquidtight strain relief, and outlet bushing. CSA certified watertight when used with 5262 Series Sealing Ring
Temperature Rating:	105 °C
Hub Size:	1-1/4 in.
Material:	Die Cast Zinc

### Dimension Information

Cable Size (min.-max.):	1.065-1.205 in.
-------------------------	-----------------