



Project: GenFuel
Location: Latham, NY

Plug Power
 968 Albany Shaker Rd
 Latham, NY 12110

Liquidtight Flexible Metal Conduit Fittings

T&B Catalog Number:

UPC Number: 5335-HT
 78621090966
Status: Active
Description:

1-1/4 in. straight steel insulated liquidtight high temperature connector.

Features

	Sure-Tight gland deflects water away from connector and prevents "pooling" of moisture.
	Double beveled sealing ring designed with 5 unique sealing mechanisms and cannot be installed backwards
	Safe Edge ground cone provides superior bonding, stronger pullout, easy threading and conductor protection.
	Double plating for superior corrosion protection
	Heat Curled Insulator molded inside body provides excellent wire protection and easier glide of conductors through and into the fitting.

General

Style	Insulated
Trade Size (inches)	1 1/4
Material	Steel
Finish	Zinc Plating/Clear Chromate

Dimension Information

Dimension A (inches)	2 9/32
Dimension B (inches)	2 1/2
Dimension C (inches)	13/16

Specifications

3dmodel	Available on Website
---------	----------------------

Packaging

T&B Inner Pack	5
Package in Units	25
T&B Sold in UOM	Each
T&B Weight Per UOM	67.4 lbs. per 100

Application Support

304 Stainless Steel Corrosion Compatibility Chart - Available on Website

T&B Sales Drawings	wsd-000016
T&B Instruction Sheets	ta02544-tb2

Certifications



File Nbr:
E 23018

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com