



Liquidtight Flexible Cord & Cable Fittings

T&B Catalog Number:

CC-NPT-12-G-2

UPC Number:

78621091575

Status:

Active

Description:

1/2 in. gray non-metallic multi-hole cord grip connector with 2 openings. Thread length-.590 in.; cable range-.190-.250.

Features

Sturdy cable sealing mechanism which results in superior strain relief.

Compact size ensures quick and easy installation in cramped spaces

Non-metallic construction provides excellent corrosion, chemical and impact resistance.

General

Material	Polyamide 6
Color	Gray
Number of Openings	2

Dimension Information

Hub Size (inches)	1/2
Cable Range-Minimum (inches)	0.19
Cable Range-Maximum (inches)	0.25
Body Length-Minimum (inches)	1.051
Body Length-Maximum (inches)	1.291
Thread Length (inches)	0.59

Specifications

3dmodel	Available on Website
Temperature Rating	+276 F-intermittent, -86 F to 176 F-continuous

Packaging

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	250
T&B Sold in UOM	Each
T&B Weight Per UOM	3.94 lbs. per 100

Application Support

T&B Sales Drawings	wsd-000375
T&B Instruction Sheets	ta02021-tb2
Product Overview	Available on Website
Portable Cord Selection Table	Available on Website

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
E 13938

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com