



Project: COMET

Russellstoll

MaxGard Interconnection Systems

T&B Catalog Number:

DF2404FRAB0

UPC Number:

70891715870

Status:

Active

Description:

MaxGard? Female Receptacle with Angle Adapter and Junction Box, 200 Amp, 3 Pole 4 Wire, 3? 480V, 60Hz

Features

Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight").

Two optional pilot/control pins for contractors, load monitor circuits, shunt trip or any other communication functions you need.

Center ground contacts: make FIRST, break LAST
All receptacles and connectors have a gated rotating disk on the face of the interior, engaged on insertion.

Application

Electrical hook-up of mobile medical imaging (MMI) trailers.

For use in applications where outdoor, severe or high abuse environments exist.

Electrical hook-up of mobile medical imaging (MMI) trailers.

General

Style	Load Breaking Female Receptacle
Material	Copper Free, Cast Aluminum, Epoxy Powder-Coated Housing
Material_1	Standard Neoprene O-ring interior components
Frequency	60 Hz
Amperage	200 Amp
Pole/Wire	3P/4W
System	Heavy Industrial & Marine

Dimension Information

Overall Dimensions Available on Website

Specifications

Voltage 3 Phase 480 Volts AC
Engineering Specifications Available on Website

Packaging

Package in Units	1
T&B Sold in UOM	Each
T&B Weight Per UOM	26.2 lbs. Each

Application Support

Overview	Available on Website
Russellstoll Application Guide	Available on Website

Notes

To order a straight adapter, update the 'A' to 'S'. i.e.
Angled Adapter Catalog Number-DS4104MRA00,
Straight Adapter Catalog Number-DS4104MRS00.

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com