

**Riser-Gard Flexible Raceway**

**T&B Catalog Number:**

DF4X1-250S

**UPC Number:**

79120721316

**Status:**

Active

**Description:**

1 Inch Riser-Gard orange corrugated non-metallic flexible raceway (split), coil length-250 foot.

**Features**

UL Listed and is available with tape pre-installed.  
Listed to UL 2024 in accordance with the National Electrical Code per Articles 725, 770, 800 and 820 for Riser, General Purpose and other cabling optical fiber/telecommunication applications.  
FT-4 Rated

**Application**

Riser-Gard is suitable for use in vertical runs in a shaft or between floors, as well as areas other than the plenum.  
Riser and general purpose applications

**General**

Material	Non-Metallic
Color	Orange
Reel Length (feet)	250
Storage Temperatures	-4 degree F to 158 degree F
Handling Temperatures	-4 degree to 104 degree F
Pull Tape (lbs)	Empty/Split

**Dimension Information**

Size (inches)	1
Coil Length (feet)	250
Minimum Bend Radius (inches)	6
Minimum O.D. (inches)	1.29
Maximum O. D. (inches)	1.34

**Packaging**

T&B Order Multiple	250
Package in Units	250
T&B Sold in UOM	Feet
T&B Weight Per UOM	13.63 lbs. per 100

**Application Support**

T&B Sales Drawings	wsd-ac04182
--------------------	-------------

**Certifications**

RoHS Compliance	Yes
-----------------	-----

**Certifications**



File Nbr:  
E 13938

For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)