



Project: Disney
Location: Florida

Crescent Electric Supply

Russellstoll

Russellstoll Hazardous Locations

T&B Catalog Number:

DS1404MP000

UPC Number:

70891716839

Status:

Active

Description:

MaxGard? Screw Cap Male Plug, 3 Pole 4 Wire, 100 Amp, 3? 480V-60Hz

Features

Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight").

Two optional pilot/control pins for contractors, load monitor circuits, shunt trip or any other communication functions you need.

Center ground contacts: make FIRST, break LAST
Standard delayed action pull and turn withdrawal offers all plugs an XP rating (30-100 amps).

Application

Convention centers and arenas

For use in applications where outdoor, severe or high abuse environments exist.

Convention centers and arenas

General

Style	Load Breaking Male Plug
Material	Copper Free, Cast Aluminum, Epoxy Powder-Coated Housing
Material_1	Standard Neoprene O-ring interior components
Material_2	Pin and sleeves are made from CDA 360 and Marine-grade CDA 485 brass (200a nd 400 amp lines are silver-plated as well).
Frequency	60 Hz
Amperage	100 Amp
Pole/Wire	3P/4W
System	Hazardous Locations

Dimension Information

Overall Dimensions Available on Website

Specifications

Voltage	3 Phase 480 Volts AC
Engineering Specifications	Available on Website

Packaging

Package in Units	1
T&B Sold in UOM	Each



T&B Weight Per UOM 4.8 lbs. Each

Application Support

Overview	Available on Website
Russellstoll Application Guide	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com