

Russellstoll

MaxGard Interconnection Systems

T&B Catalog Number:

DS2404MP000

UPC Number:

70891715982

Status:

Active

Description:

MaxGard? Male Plug, 200 Amp, 3 Pole 4 Wire, 3? 480V, 60Hz

Features

Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight").

Two optional pilot/control pins for contractors, load monitor circuits, shunt trip or any other communication functions you need.

Center ground contacts: make FIRST, break LAST
Standard delayed action pull and turn withdrawal offers all plugs an XP rating (30-100 amps).

Application

Electrical hook-up of mobile medical imaging (MMI trailers).

For use in applications where outdoor, severe or high abuse environments exist.

Electrical hook-up of mobile medical imaging (MMI trailers).

General

Style	Load Breaking Male Plug
Material	Copper Free, Cast Aluminum, Epoxy Powder-Coated Housing
Material_1	Standard Neoprene O-ring interior components
Material_2	Pin and sleeves are made from CDA 360 and Marine-grade CDA 485 brass (200a nd 400 amp lines are silver-plated as well).
Frequency	60 Hz
Amperage	200 Amp
Pole/Wire	3P/4W
System	Heavy Industrial & Marine

Dimension Information

Overall Dimensions	Available on Website
--------------------	----------------------

Specifications

Voltage	3 Phase 480 Volts AC
Engineering Specifications	Available on Website

Packaging

Package in Units	1
T&B Sold in UOM	Each
T&B Weight Per UOM	11.5 lbs. Each

Application Support

Overview	Available on Website
Russellstoll Application Guide	Available on Website



For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com