



Solar Clip
T&B Catalog Number:

GD-001-TB

UPC Number:

78620999988

Status:

Active

Description:

Cable Edge 90 Degree Solar Clip, Heat-Stabilized Nylon 6.6

Features

Mount up to four #10 AWG Solar PV control cables cleanly and easily - keeping a professional look through panel rotation and vibration.

Provides the ability to quickly slip the cables in and out of the clamp for ice removal, readjustment or other maintenance.

Quick and easy installation, no tools required. Metal-free construction reduces the need for grounding.

Perfect for strength stability in heat of solar applications.

Application

Solar Panel projects.

General

Material	Nylon 6.6 Heat-Stabilized
Color	Black
Mounting Method	Clip

Dimension Information

Length (inches)	1.59
Width (inches)	1.00
Height (inches)	1.34

Specifications

Temperature Rating	-40°F to 220°F
Flammability Rating	UL 94 V-2

Packaging

T&B Order Multiple	100
T&B Inner Pack	100
Package in Units	1000
T&B Sold in UOM	Each
T&B Weight Per UOM	2.38 lbs. per 100

Application Support

T&B Sales Drawings	wsd-001092
--------------------	------------

Notes

Fits frame thickness range .060 - .120 inches. Maximum cable diameter .31 inches.

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289

