



Heavy-Duty T&B Catalog Number:

UPC Number:

Status:

Description:

L-24-120-0-Q

78621008064

Active

Cable Tie 120lb 24" Ultraviolet Resistant Black All-Nylon Dist Pack

General

Material	Nylon 6.6 Weather Resistant
Color	Black

Dimension Information

Nominal Length (inches)	24
Length (inches)	24.2
Width (inches)	0.300
Max. Wire Bundle Diameter (inches)	7
Min. Wire Bundle Diameter (inches)	3/16

Specifications

Temperature Rating	-40°F to 185°F
Flammability Rating	UL 94 V-2

Tooling

Application Tools	ERG120
-------------------	--------

Packaging

T&B Order Multiple	500
T&B Inner Pack	25
Package in Units	500
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	2.5 lbs. per 100

Application Support

Overview	Available on Website
Material Selection Guide	Available on Website
Available Colors	Available on Website

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com