



Extra Heavy-Duty T&B Catalog Number:

UPC Number:

Status:

Description:

L-24-175-0-L

72849491280

Active

Cable Tie 175lb 24" Ultraviolet Resistant Black All-Nylon 50 Per Bag

General

Material	Nylon 6.6 Weather Resistant
Color	Black

Dimension Information

Nominal Length (inches)	24
Length (inches)	24.0
Width (inches)	0.345
Max. Wire Bundle Diameter (inches)	7.2
Min. Wire Bundle Diameter (inches)	3/16

Specifications

Temperature Rating	-40°F to 185°F
Flammability Rating	UL 94 V-2

Tooling

Application Tools	L-300C
-------------------	--------

Packaging

T&B Order Multiple	500
T&B Inner Pack	50
Package in Units	500
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	2.5 lbs. per 100

Application Support

T&B Sales Drawings	wsd-000289
Overview	Available on Website
Material Selection Guide	Available on Website
Available Colors	Available on Website

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com