

**Mounting Head**
T&B Catalog Number:

L-7-50MH-0-C

UPC Number:

72849491660

Status:

Active

Description:Cable Tie 50lb 7" Ultraviolet Resistant Black All-Nylon #10 Mounting Hole
100 Per Bag**General**

Material	Nylon 6.6 Weather Resistant
Color	Black
Mounting Hole Size	#10

Dimension Information

Nominal Length (inches)	7
Length (inches)	7.5
Width (inches)	0.185
Max. Wire Bundle Diameter (inches)	1 3/4
Min. Wire Bundle Diameter (inches)	1/16

Specifications

Temperature Rating	-40°F to 185°F
Flammability Rating	UL 94 V-2

Tooling

Application Tools	ERG50, ERG120, QC-100, L-200, L-400-C
-------------------	---------------------------------------

Packaging

T&B Order Multiple	100
T&B Inner Pack	100
Package in Units	5000
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	3.75 lbs. per 1000

Application Support

T&B Sales Drawings	wsd-000303
Overview	Available on Website
Material Selection Guide	Available on Website
Available Colors	Available on Website

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications**For further technical assistance, please contact us...**Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.comT&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com