Intermediate
T&B Catalog Number: TY125-40X
UPC Number: 78621089856
Status: Active
Description:

Cable Tie 40lb 5" Ultraviolet Resistant Black All-Nylon 1000 Per Bag

Features

The integrally formed nylon pawl combines low insertion and high locking strength.

Standards

UL Recognized

General

Material	Nylon 6.6 Weather Resistant
Color	Black

Dimension Information

Nominal Length (inches)	5
Length (inches)	5.6
Width (inches)	0.130
Max. Wire Bundle Diameter (inches)	1 1/4
Min. Wire Bundle Diameter (inches)	1/16

Specifications

Temperature Rating	-40°F to 185°F
Flammability Rating	UL 94 V-2

Tooling

Application Tools	ERG50, QC-100, L-200, L-400-C

Packaging

T&B Order Multiple	1000
T&B Inner Pack	1000
Package in Units	10000
T&B Sold in UOM	Each
T&B Weight Per UOM	1.39 lbs. per 1000

Certifications

RoHS Compliance	Yes

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com