



Standard
T&B Catalog Number:

TY27M-8
78621084506
Active

UPC Number:
Status:
Description:

Cable Tie 120lb 13" Gray Nylon with Stainless Steel Locking Device Bulk Pk, Military Specified (MIL-SPEC MS3367-3-8)

Features

Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulk-heads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.

Because there are no notches, Ty-Rap ties provide an infinite number of locking positions while fastening the tie at the precise bundle diameter needed.

The No-Slip Tail provides easy grip during tensioning. Ty-Rap ties feature a unique friction surface designed to reduce slippage during installation.

Smooth, notchless body reduces stress concentration points under tension, making the tie stronger and lower profile than notched body ties. Ribbed and Stippled body grips the bundle and prevents slippage. Rounded edges protect insulation, preventing sharp edges from damaging cables.

General

Material Nylon 6.6
Color Gray

Dimension Information

Nominal Length (inches) 13
Length (inches) 13.4
Width (inches) .270
Max. Wire Bundle Diameter (inches) 3.5

Specifications

Temperature Rating -40°F to 185°F
Flammability Rating UL 94 V-2

Tooling

Application Tools WT197, ERG120

Packaging

T&B Order Multiple 500
T&B Inner Pack 500
Package in Units 1000
Package Type Bulk
T&B Sold in UOM Each
T&B Weight Per UOM 1 lbs. per 100

Application Support

Material Selection Guide Available on Website
Available Colors Available on Website

Certifications

RoHS Compliance

Yes

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com