

Lashing Tie
T&B Catalog Number:

TY409

UPC Number:

78621082547

Status:

Active

Description:

Heavy Duty Releasable Lashing Cable Tie 200 lb. 19" Black Weather-Resistant Nylon, Width .5 in., Maximum Wire Bundle Diameter 4.75 in., Temperature Rating -40B0F to 176B0F, Bulk Pack

General

Material	Nylon 6/6 Weather Resistant
Color	Black

Dimension Information

Nominal Length (inches)	19
Length (inches)	19
Width (inches)	.500
Max. Wire Bundle Diameter (inches)	4.75

Specifications

Temperature Rating	-40°F to 185°F
--------------------	----------------

Packaging

T&B Order Multiple	100
T&B Inner Pack	100
Package in Units	500
Package Type	Regular
T&B Sold in UOM	Each
T&B Weight Per UOM	3.31 lbs. per 100

Application Support

Overview	Available on Website
Material Selection Guide	Available on Website

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com