



## Wiring Duct T&B Catalog Number:

**UPC Number:**  
**Status:**  
**Description:**

TY4X4WHW6  
78620988483  
Active

## Wiring Duct Halogen Free Wide Slot 4 Inch X 4 Inch Modified PPE White Features

Higher temperature rating than PVC. Wide fingers and slots increase rigidity and enable insertion of bundles. V-Shaped slot lead-in enables easier and faster wire installation. Rounded edges keep hands and wires free of abrasion.

Non-slip cover does not slide easily and resists vibration. Flush cover attaches flush with sidewall for finished look.

Dual score lines are designed to yield clean breakoffs at the base of the slot and the duct. Versatile North American and DIN Standard mounding holes enables same duct for multiple applications.

## General

Style	Wide Slot, Halogen-Free
Nominal Width (inches)	4
Nominal Height (inches)	4
Material	Modified PPE
Color	White
Adhesive-Backed	No
Mounting Holes	Yes

## Dimension Information

Length (feet)	6
Width (inches)	4.25
Height (inches)	4.46
A (inches)	4.25
B (inches)	4.46
C (inches)	4.25
D (inches)	4.39
E (inches)	0.3
F (inches)	3.63
G (inches)	0.39
H (inches)	0.1
I (inches)	1

## Accessories & Components

Cover	TY4CHW6
-------	---------

## Packaging

T&B Order Multiple	30
T&B Inner Pack	6
Package in Units	30
T&B Sold in UOM	Feet
T&B Weight Per UOM	60 lbs. per 100

## Application Support

T&B Sales Drawings	wsd-000283
Technical Information	Available on Website

Specifications	Available on Website
Overview	Available on Website
Wire Fill Calculator	Available on Website

## Notes

Standard lengths are 6 feet.

## Certifications

RoHS Compliance	Yes
Webcat CE_recognized	Y

## Certifications



### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)