



Standard

T&B Catalog Number:

TY525M-CLRS

UPC Number:

78621093245

Status:

Active

Description:

Cable Tie 50lb 7" Natural Nylon Multi-Colored with Stainless Steel Locking Device, 10 of each Standard Color

Features

Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulk-heads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.

Because there are no notches, Ty-Rap ties provide an infinite number of locking positions while fastening the tie at the precise bundle diameter needed.

The No-Slip Tail provides easy grip during tensioning. Ty-Rap ties feature a unique friction surface designed to reduce slippage during installation.

Smooth, notchless body reduces stress concentration points under tension, making the tie stronger and lower profile than notched body ties. Ribbed and Stippled body grips the bundle and prevents slippage. Rounded edges protect insulation, preventing sharp edges from damaging cables.

General

Material	Nylon 6.6
Color	Assortment

Dimension Information

Nominal Length (inches)	7
Length (inches)	7.31
Width (inches)	.184
Max. Wire Bundle Diameter (inches)	1.75

Specifications

Temperature Rating	-40°F to 185°F
Flammability Rating	UL 94 V-2

Tooling

Application Tools	ERG-299, WT1-TB
-------------------	-----------------

Packaging

T&B Order Multiple	100
T&B Inner Pack	100
Package in Units	1000
Package Type	Regular
T&B Sold in UOM	Each
T&B Weight Per UOM	3.13 lbs. per 1000

Application Support

Material Selection Guide	Available on Website
Available Colors	Available on Website

Notes

10 of each standard color

Certifications

RoHS Compliance

Yes

Certifications



File Nbr:

Y

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com