

# KT-4GFXS Biometric Solutions

#### Features That Make a Difference:

- Large Template Storage Capacity (10,000 in 1:N; 100,000 in 1:1)
- Integrated ioProx Card Readers
- Range of 500 DPI Sensor Options Field Replaceable Sensors
- Backwards Compatible
- Remote Device Management
- IP Connectivity (LAN, WAN, PoE)
- Easy Administration with SecurAdmin™
- Flush or Recess Mounted



## Power and Flexibility Features at a glance in a Compact Design

Need a compact device but still require strong biometric capabilities and deployment flexibility? V-Flex 4G XSF and W26 fingerprint is the right solution for you. A variety of models are available on demand to address a wide range of deployment scenarios. Quick throughput, deployment flexibility, and the ability for the system to expand over time meet the demands of today and will be drivers for future requirements. Ensure employees gain access fast, 4G searches 6,000 templates per second

#### Meet Challenging Security Requirements

A full range of options are available for different security requirements. Remove install constraints with a wide range of configurable options for multi-factor authentication with multi-factor authentication combining fingerprint, cards and PINs.

#### **Reduce Maintenance Costs**

Save time and drive down the cost of ownership with a communication-ready connected smart device, contain new installation and maintenance capabilities.

- Leverage the latest communication standards – Full Ethernet, PoE, RS485
- Maintenance is quick and easy with our Innovative field replaceable sensor modules.
- Take full advantage of IP connectivity for Remote device management.

# Leverage Existing Infrastructure

Confront migration costs and effort with a device that is backwards compatible and purpose built to work with security industry technologies.

 Eliminate the need for re-enrollment with support for all Bioscrypt legacy template formats



#### **Specifications**

**Dimensions** 

Recessed Mounted..... 159 mm x 96 mm x 48 mm 6.27 in x 3.8 in x 1.89 in  $(H \times W \times D)$ 159 mm x 96 mm x 65 mm Flushed Mounted .... 6.27 in x 3.8 in x 2.56 in  $(H \times W \times D)$ 

Communications

Networking Options. . . . . LAN, WAN, RS485 PC Connection . . . . . . USB, RS232

External Media

USB memory. . . . . . . . External Media USB memory

Input / Outputs

Wiegand (Customizable

3 General Purpose Inputs format up to 256 bits) . . . . 3 General Purpose Outputs (Extendable to 6 outputs)

Fingerprint Sensor

Options . . . . Internal Card UPEK TCS1, Secugen Optical (All 500 dpi)

KT-4GFXS-IO-W26, 4G biometric reader with Reader Options . . . . integrated ioProx 26bit Wiegand reader KT-4GFXS-IO-XSF, 4G biometric reader with

integrated ioProx XSF reader

Template Storage

V-Flex 4G (ioProx) - Store 100,000 templates for 1:1 Capacity . . . . . . . .

verification or 10,000 templates for 1:N identification Transaction Log

Capacity . . . . . . . . . 1 Million transaction logs stored on device

**Authentication Modes** 

V-Flex 4G (ioProx) . . . . . . Prox Card + Finger Prox Card Only Finger Only

Template Support . . . . . . Bioscrypt Pattern and Minutia

Power over

Ethernet (PoE) . . . . . . . . Standard 12 - 24V DC 

Power Indicator . . . . . . LED indicator (Blue)

Integrated Door Relay . . . . Deadbolt, electromagnetic (EM) lock, door strike,

automatic door

Recessed or Flush mount with field replaceable Mounting.....

sensors for easy maintenance Operating Temperature . . . 32° - 140°F (0° - 60°C)

Regulatory Approvals

and Certifications. . . . . . . FCC, CE , R&TTE, RoHS

Administration Software

Options . . . . . . . . . . . . . . . . . . Works with SecureAdmin $^{\text{TM}}$  software or

SecureSDK™

Model Number	Description
KT-4GFXS-IO-W26	4G biometric reader with integrated ioProx 26bit Wiegand reader
KT-4GFXS-IO-XSF	4G biometric reader with integrated ioProx XSF reader

(1) For more information: www.L1ID.com/EnterpriseAccess

### **Related Products**



ioProx Cards and Tags



ioProx Proximity Readers



KT-400 4-Door Controller



EntraPass Security Management Software

#### Approvals







www.kantech.com