

# FlexSmart® Series Credentials

## DESFire® / HID Prox Combo Card • 1451, 1457

- ▶ **Multiple Formats** - Supports all Indala proximity card formats, including FlexEnterprise®.
- ▶ **Transition Solution** - Add smart card applications to existing Indala proximity technology access control system.
- ▶ **High Security** - Mutual authentication, DES and triple-DES data encryption, and unique 56-bit serial number.



### ACCESS interoperability.

HID Proximity and FlexSmart DESFire ISO card is an extra-secure credit card-sized credential that complies with ISO 7810 and 7813 standards. It can be used for diverse applications such as access control and biometric identification, cashless vending, public transportation, ticketing, customer loyalty and photo ID cards. Available in PVC and Composite PET/PVC card construction, the HID DESFire Prox card is exceptionally durable, and can accept an embeddable contact chip for logical access and biometric ID systems.

13.56 MHz DESFire read/write technology and HID 125 kHz proximity technology are combined in a single ISO standard thickness card. This card enables contactless smart card applications to be added to an existing HID proximity technology access control system.

HID DESFire credentials have 4 KB of dynamic memory arranged in easy-to-define application folders and data files. DESFire data can be encrypted with the highly secure Data Encryption Standard (3DES) algorithm assuring that data in the card is secure before, during and after the transaction, as well as between folders and files within the credential itself.

When security and performance count most, HID's FlexSmart DESFire cards can be produced with visual security and anti-counterfeiting features such as holograms, ultra-violet fluorescent inks, micro-printing, or a custom logo to quickly and easily identify genuine cards.

#### Key Features

- ▶ **Proven, Reliable Technology** - Offers extremely consistent read range. Use is unaffected by body shielding or variable environmental conditions, even when close to keys and coins.
- ▶ **Fast Processing and Data Communication** - Transaction times are less than 100 milliseconds for a typical secure ticketing transaction.
- ▶ **True Credit Card Thickness** - Use with all direct image and thermal transfer printers.

# Features

**Long Life** Passive, no-battery design allows for an infinite number of reads.

**Durability** Strong, flexible and resistant to damage.

**Photo ID Compatible** Print directly to the card with a direct image or thermal transfer printer. Slot punch vertically for easy use.

**PVC Card Surface** Card is optimized for dye sublimation printing.

**Customizable** Specify your own text or graphics artwork.


**Thin** 0.030" (0.076 cm) card can be carried with credit cards in a wallet or purse. Use with a strap and clip as a photo ID badge.

**Many Ordering Options** Including magnetic stripe, external card numbering, vertical slot punch, custom artwork, and contact smart chip module.

<b>Dimensions</b>	2.125" x 3.375" x .03" (5.4 x 8.57 x 0.076 cm)
<b>Weight</b>	0.24 oz. ( 6.8 g )
<b>Typical Maximum Read Range*</b>	DESFire: Up to 4" (10 cm) Prox: 2" – 4.5" (5.0 – 11.4 cm)
<b>Operating Temperature</b>	Model 1451 PVC Cards: -40 to 122°F (-40 to 50°C) Model 1457 Composite Cards: -40 to 158°F (-40 to 70°C)
<b>Operating Humidity</b>	5%-95% Non-condensing
<b>Operating Frequency</b>	13.56 MHz
<b>RF Interface</b>	ISO 14443 A, Parts 1-4
<b>Transaction Time</b>	< 100 ms
<b>Baud Rate</b>	106,212 or 424 kbps
<b>Memory Type</b>	EEPROM, 4 Kbytes (32,768 bits)
<b>Multi-Application Memory</b>	Dynamic Memory structure, up to 28 applications
<b>Write Endurance</b>	100,000 cycles min.
<b>Data Retention</b>	10 years min.
<b>Material and Finish</b>	Gloss white/white PVC or PVC/Polyester Composite
<b>Card Marking</b>	Inkjet Standard, Laser Engraving optional
<b>Custom Graphics</b>	Optional
<b>Slot Punch</b>	Vertical slot punch optional
<b>Programming</b>	Factory or Field Programmable
<b>Part Number</b>	Model 1451 PVC DESFire Prox Card Model 1457 Composite PET/PVC DESFire Prox Card
<b>Description</b>	DESFire / HID Prox Combo Card, ISO Thick, Photo Imageable
<b>Warranty</b>	Lifetime - see Sales Policy for complete details

\*Dependent on local installation conditions.

© 2007 HID Global Corporation. All rights reserved. HID, the HID logo, and FlexSmart are trademarks or registered trademarks of HID Global in the U.S. and/or other countries. All other trademarks, service marks, and product or service names are trademarks or registered trademarks of their respective owners. Rev. 4/2007



MKT-DESPROX-DS-EN



**ACCESS** experience.

[hidcorp.com](http://hidcorp.com)

**HID Global Offices:**

**Corporate North America**  
9292 Jeronimo Road  
Irvine, CA 92618-1905  
U.S.A.  
Phone: (800) 237-7769  
Phone: (949) 598-1600  
Fax: (949) 598-1690

**Asia Pacific**  
19/F 625 King's Road  
North Point  
Island East  
Hong Kong  
Phone: +852 3160-9800  
Fax: +852 3160-4809

**Latin America**  
Circunvalacion Ote. #201 B  
Despacho 2  
Col. Jardines del Moral  
Leon 37160, Gto.  
Mexico  
Phone: +52 477 779 1492  
Fax: +52 477 779 1493

**Europe, Middle East & Africa**  
Homefield Road  
Haverhill, Suffolk  
CB9 8QP  
England  
Phone: +44 (0) 1440 714 850  
Fax: +44 (0) 1440 714 840