FlexSmart® Series Credentials DESFire® Keyfob • 1454

FlexKey Flexibility and Convenience - Contemporary design enables easy attachment to a key, badge clip or badge lanyard.

Rugged, Double-Sealed Construction - Built to withstand harsh operating environments.

Customizable - Can be customized by adding a company logo.



ACCESS interoperability.

The rugged HID FlexSmart DESFire Keyfob is ideally suited for a variety of applications and environments. These include vacation resorts, health spas, apartment buildings, club houses, as well as commercial offices where photo IDs are not required. The HID DESFire Keyfob permits the encoding of a wide range of data and information, featuring the high quality and security benefits customers appreciate in HID 13.56 MHz DESFire credentials.

HID DESFire credentials have 4K of dynamic memory arranged in easy-to-define application folders and data files. DESFire data can be encrypted with the highly secure Data Encryption Standard (3DES) algorithm providing the confidence that data in the card is secure before, during and after the transaction, as well as between folders and files within the credential itself.

Key Features

- ▶ High Security DESFire technology includes mutual authentication, DES and triple-DES data encryption, and unique 56-bit serial number.
- ▶ Proven, Reliable Technology Offers extremely consistent read range. Use is unaffected by body shielding or variable environmental conditions, even when close to keys and coins.
- ▶ Fast Processing and Data Communication Transaction times are less than 100 milliseconds for a typical secure ticketing transaction.

Features

Long Life

Passive, no-battery design allows for 100,000 read/write

Rugged and Durable Design

Able to withstand harsh environments, the MIFARE® Keyfob® has double-sealed construction. Inner electronics are fully encapsulated in epoxy. Outer body is an ultra-sonic welded, polycarbonate material.

Applications


Designed for vacation resorts, health spas, apartment buildings, locker rooms, gated communities, vehicle fleet management, and corporate environments.

Dimensions	1.725" × 1.197" × 0.215" (4.38 cm × 3.04 cm × 0.55 cm)
Weight	0.191 oz. (5.4 g)
Typical Maximum Read Range*	Up to 2" (5.0 cm)
Operating Temperature	-40 to 158°F (-40 to 70°C)
Operating Humidity	5%-95% Non-condensing
Operating Frequency	13.56 MHz
RF Interface	ISO 14443 A, Parts 1-3
Transaction Time	< 100 ms
Baud Rate	106, 212 or 424 kbps
Memory Type	EEPROM, 4 Kbytes (32,768 bits)
Multi-Application Memory	Dynamic Memory structure, up to 28 applications
Write Endurance	100,000 cycles min.
Data Retention	10 years min.
Material and Finish	Molded Polycarbonate, matte blue
Card Marking	Inkjet Standard, laser engraving optional.
Custom Graphics	Optional
Slot Punch	Key Ring Hole
Programming	Factory or Field Programmable
Part Number	Model 1454 FlexSmart DESFire FlexKey
Description	DESFire Keyfob
Warranty	Lifetime - see Sales Policy for complete details
	*Dependent on local installation conditions.



ACCESS experience.

© 2007 HID Global Corporation.All rights reserved. HID, the HID logo, and FlexSmart are trademarks or registered trademarks of HID Global in the U.S. and/or other countries. All other trademarks, service marks, and product or service names are trademarks or registered trademarks of their respective owners. Rev. 4/2007



MKT-DESFIRE-KEYFOB-DS-EN

hidcorp.com

HID Global Offices:

Latin America
Circunvalacion Ote. #201 B
Despacho 2
Col. Jardines del Moral
Leon 37160, Gto.
Mexico
Phone: +52 477 779 1492
Fax: +52 477 779 1493

Europe, Middle East & Africa Homefield Road Haverhill, Suffolk CB9 8QP England