



## LED-1908HD

This LED-backlit free standing monitor features the latest technology with enhanced picture clarity and sharpness for both analog and digital video signals.

### Benefits

- Analog video is very clear with no detail loss
- Displays 1080i/p digital video
- 3D Comb Filter for better picture quality
- High contrast ratio for better picture definition
- Durable metal case
- Desk stand, VESA pattern, and keyholes for wall-mounting

### Accessories

- DC-1500: Factory approved car cord
- HM-400: Under-cabinet hinge mount
- WM-31: Wall mount bracket (fixed)
- WM-302: Wall mount with swing arm & 4-way adjustable
- WMC-2342: Ceiling mount bracket for 1.5" NPT pipe (order with WM-31)

### Related Products

- LED-1908HDL: 19" flush-mount LCD Monitor
- LED-1908HDR: 19" rack-mount LCD Monitor
- LED-1908HDVB: 19" standalone / wall-mount LCD High Brightness Monitor
- LED-1708HD: 17" standalone / wall-mount LCD Monitor
- LED-1708HDL: 17" flush-mount LCD Monitor
- LED-1708HDR: 17" rack-mount LCD Monitor



Specifications	
Mount	VESA 100mm X 100mm; Removable Deskstand
HD Compatible	Yes
Anti Glare Coating	Yes
Case	Durable Metal
Native Aspect Ratio	5:4
Visible Screen Size (WH)	376.3 x 301mm / 14.8" x 11.8"
Resolution	1280(H) x 1024(V)
Brightness Rating	1,000 cd/m <sup>2</sup>
Contrast Ratio	10,000:1
Back Light	LED
PC Compatibility	Yes
Dot Pitch	0.294(H) x 0.294(V)mm
Color Depth	16.7M
Number of Pixels	1,310,720
Response Time	5ms (Rising/Falling)
Audio Power / Speakers	x2 1.5 Watts
Viewing Angle (L/R/T/B)	85/85/80/80 degrees
3D Comb Filter	Yes
Dimensions	16.4" x 14.5" x 2.9" / 415.5 x 366.7 x 72mm
Operating Temp	32 ~ 104°F / 0 ~ 40°C
Humidity	10% ~ 90%
Power Requirements	DC 12V (AC100~240)[50/60]
Power Consumption	15 Watts (Max)
Composite	x2 BNC Inputs / Outputs
PC	x1 VGA 15-pin D-sub Input / Output
HDMI	Yes
Audio	x1 RCA Input; x1 PC stereo Input
Power	x1 2.1mm DC Input
Weight	Net: 10.2 lbs / 4.7 kg; Gross: 15.7 lbs / 7.1 kg

Specifications subject to change.