

180XL VISUAL FAULT LOCATOR

FAST AND EASY FAULT FINDING

fiberTOOLS™

EFFICIENT.

QUICKLY AND EASILY LOCATE
HIGH LOSSES AND FAULTS IN
FIBER OPTIC CABLES

EXTENDED REACH.

UP TO 7km MEASUREMENT
RANGE

VERSATILE.

PULSED AND CW MODE
OF OPERATIONS



180XL

VISUAL FAULT LOCATOR

FOR PRODUCT VIDEOS, DEMONSTRATIONS
AND MORE, SCAN THIS QR CODE OR VISIT:
www.youtube.com/GreenleeDEMO



SPECIFICATIONS

Wavelength	650nm +/-10nm
Emitter Type	Fabry Perot
Output Power	0dBm
Laser Classification	Class 2
Range	7km
Modes of Operation	CW and 2Hz Modulation
Method of Display Operation	Red/Green LED
Fiber Type	Singlemode, Multimode
Connector Interface	2.5mm Universal, Optional 1.25mm adapter
Battery	AA (2 included)
Battery Life	80 Hours with 3.9Wh Batteries
Weight	0.26lbs, (120g) (not including batteries)
Dimensions	7.08" x 0.91" Dia (180mm x 23mm Dia)
Operating Temperature	-10°C to +45°C
Storage Temperature	-40°C to +70°C
Certifications	CE, CDRH



ORDERING INFORMATION

CAT NO.	DESCRIPTION
180XL	Visual Fault Locator
1.25mm Adapter	1.25mm Adapter for LC and MU connectors



www.greenlee.com MA6247 12/14

1390 Aspen Way Vista, CA • 92081 • tel 800.642.2155

©2014 Greenlee Textron Inc. • An ISO 9001 Company • Printed in USA

Greenlee Textron Inc. is a subsidiary of Textron Inc.

