

T30L5C2



Article Number: 111-01325

Standard Cable Tie, 7.8" Long, 30lb Tensile Strength, PA66, Green, 100/pkg

 **RoHS**



[Download spec sheet](#)

Base Data

Local Order Number	T30L5C2
Type	T30L
Color	Green (GN)
Features and Benefits	• Inside serrations allow for strong hold on cables and wire bundles. • Head design provides high tensile strength with very low insertion force. • Bent tail ensures a quick and simple installation.
Product Description	HellermannTyton standard cable ties feature inside serrations providing a positive hold onto wire and cable bundles. The head design guarantees high tensile strength, as well as a low insertion force. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.
Short Description	Standard Cable Tie, 7.8" Long, 30lb Tensile Strength, PA66, Green, 100/pkg

Product Dimensions

Minimum Tensile Strength (Imperial)	30.0 lbs
Minimum Tensile Strength (Metric)	135.0 N
Length L (Imperial)	7.48 "
Length L (Metric)	198.0 mm
Fixation Method	None
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.138 "
Width W (Metric)	3.6 mm
Bundle Diameter Min. (Imperial)	0.059 "
Bundle Diameter Min. (Metric)	1.5 mm
Bundle Diameter Max. (Imperial)	1.97 "
Bundle Diameter Max. (Metric)	50.0 mm

Logistics and Packaging

Package Quantity (Metric)	100
---------------------------	-----

Material and Specifications

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66

Flammability UL94 V2

Halogenfree Yes

Operating Temperature -40°F to +185°F (-40°C to +85°C)

ROHS Compliant Yes

UL Listed (US and Canada) Yes

UL Recognized (US and Canada) Yes