



FPR3SP loaded with FSPST6, FSPSCD3
and FSPSCD03 adapter panels.



- Cost Effective 1U Design in Pre-Punched or FSP Panel Mounting Configurations
- Hinged Swing-Out Drawer for Easy Installation and Access
- CSI Specifications and Drawings Available
- Low Density 1U Space-Saving Design

Specifications

- Material: 16ga cold rolled steel
- Finish: durable black powder coat
- Splice tray capacity: maximum 2

Standards/Listings/Verifications

- EIA-310-E
- TIA-569-C
- TIA-604-FOCIS

FPR – Pre-Punched Enclosures (Loaded)

Rack Units	Height Inches (mm)	Width Inches (mm)	Depth Inches (mm)	Connector Type	Port Capacity	No. of Adapters	Catalog No.*
1	1.75" (44)	17" (432)	11" (279)	ST-style	12	12	FPR012STM
1	1.75" (44)	17" (432)	11" (279)	ST-style	24	24	FPR024STM
1	1.75" (44)	17" (432)	11" (279)	SC duplex	12	6	FPR012SCM
1	1.75" (44)	17" (432)	11" (279)	SC duplex	24	12	FPR024SCM



FPR012STM



FPR012SCX



FPR024STX



FPR3SP loaded with
FSP Series panels

FPR – Pre-Punched Enclosures (Unloaded)

Rack Units	Height Inches (mm)	Width Inches (mm)	Depth Inches (mm)	Connector Type	Port Capacity	No. of Adapters	Catalog No.*
1	1.75" (44)	17" (432)	11" (279)	ST-style	12	12	FPR012STX
1	1.75" (44)	17" (432)	11" (279)	ST-style	24	24	FPR024STX
1	1.75" (44)	17" (432)	11" (279)	SC duplex	12	6	FPR012SCX
1	1.75" (44)	17" (432)	11" (279)	SC duplex	24	12	FPR024SCX

Note: Contact Hubbell Premise Wiring for other configurations, custom made to order.
See page G8 for screw-mount SC duplex and LC quad adapters.

FPR – Pre-Punched Enclosures, FSP Panel Style (Unloaded)

Rack Units	Height Inches (mm)	Width Inches (mm)	Depth Inches (mm)	Panel Capacity	Maximum LC Port Capacity*	Catalog No.*
1	1.75" (44)	17" (432)	11" (279)	3	72	FPR3SP
1	1.75" (44)	17" (432)	11" (279)	3	72	FPR3SPNA*

*NAFTA version.

Note: See page G11 for FSP adapter panels.

Cable Management Bracket (Fits all FPR series panels)

Description	Catalog No.
Protective bracket/cable management bar	FPRBRKT1



FPRBRKT1