



FCR350SE

FCR350SE splice enclosure shown with splice trays and cables installed (front cover removed and tray extended). Splice trays sold separately.

## HUBBELL Advantage

- Patented Gasketless Routing Knockouts
- Contractor-Friendly Installation, Labeling, Cable Management, and Splice Storage
- CSI Specifications and Drawings Available
- Wide Density Range to Consolidate Space

### Specifications

- Material: 16ga cold rolled steel
- Finish: durable black powder coat

### Standards/Listings/Verifications

- EIA-310-E
- TIA-569-C

### Splice Enclosure and Hinged Rack Mount Splice Shelf

Rack Units	Height Inches (mm)	Width Inches (mm)	Depth Inches (mm)	Splice Tray Capacity	Catalog No.*
1	1.75" (44)	17" (432)	11" (279)	2	<b>FSS01S</b>
2	3.5" (89)	17" (432)	11" (279)	6	<b>FCR350SE</b>
2	3.5" (89)	17" (432)	11" (279)	6	<b>FSS02S</b>

Note: Splice trays not included.



FSS01S

### Splice Trays

No. of Fibers	Height Inches (mm)	Width Inches (mm)	Length Inches (mm)	Type	Catalog No.*
12	.4" (10)	5" (127)	7" (178)	Fusion	<b>STRAY12F</b>
12	.4" (10)	5" (127)	7" (178)	Mechanical	<b>STRAY12M</b>
24	.4" (10)	5" (127)	10" (254)	Fusion	<b>STRAY24F</b>
24	.4" (10)	5" (127)	10" (254)	Mechanical	<b>STRAY24M</b>
144	.4" (10)	5" (127)	10" (254)	(12X12 Ribbon)	<b>STRAY12RFS</b>
144	.4" (10)	5" (127)	10" (254)	(12X12 Ribbon, Deep)	<b>STRAY12RFSDP</b>



STRAY24F



STRAY12F

### Splice Protection Sleeves

Fiber Type	Sleeve Length	Cleave Length	Sleeve Diameter After Shrink	Catalog No.
Single, up to 900μm coating	40mm	10mm	3.1mm	<b>FSHST401025</b>
12-fiber ribbon	40mm	10mm	4.5mm	<b>FRSHST401025</b>



FSHST401025



FRSHST401025