



HUBBELL
Advantage

- **Modular System** — Easily Configured for New and Existing Cable Routing
- **Mounts to Floors, Walls, Ceilings, Equipment Racks and Cabinets**
- **Tip: Secure Ladder to Cabinet Tops Using J-Bolt Kit and Drilling Holes as Required**
- **RoHS Compliant**

Specifications

- Material: 16ga tubular Steel
- Durable powder coat
- Stringer dimensions: 0.375" W x 1.5" H
- Rung spacing: 9.0"
- Weight capacity: 45lb/foot

Straight Section

Width Inches (mm)	6' (1829) Length		10' (3048) Length	
	Black	Gray	Black	Gray
6" (152)	HLS0606B	HLS0606G	HLS1006B	HLS1006G
12" (305)	HLS0612B	HLS0612G	HLS1012B	HLS1012G
18" (457)	HLS0618B	HLS0618G	HLS1018B	HLS1018G
24" (610)	HLS0624B	HLS0624G	HLS1024B	HLS1024G

Note: Please order straight sections in multiples of 10 pieces.
Width = outside to outside dimensions.



90° Turns

Width Inches (mm)	Inside Radius 90° Black	Flat Turns 90° Black	Outside Radius 90° Black
6" (152)	HLI0690B	HLF0690B	HLO0690B
12" (305)	HLI1290B	HLF1290B	HLO1290B
18" (457)	HLI1890B	HLF1890B	HLO1890B
24" (610)	HLI2490B	HLF2490B	HLO2490B

Width Inches (mm)	Inside Radius 90° Gray	Flat Turns 90° Gray	Outside Radius 90° Gray
6" (152)	HLI0690G	HLF0690G	HLO0690G
12" (305)	HLI1290G	HLF1290G	HLO1290G
18" (457)	HLI1890G	HLF1890G	HLO1890G
24" (610)	HLI2490G	HLF2490G	HLO2490G



Width