



**QUADCAB® Wall Mount Cabinets**

Contents: 1 rear section (arrives disassembled facilitating installation)  
1 front door  
2 19" mounting angles

1 center section with 2 CH751 locks  
2 top/bottom cover plates  
2 hinge pins  
2 security cotter pins

Rack Units	Height	Width	Depth	Door Style	Color*	RWU**	Catalog No.
12	24" (610)	22.6" (574)	20" (508)	Window	Black	2	<b>HSQ24</b>
12	24" (610)	22.6" (574)	26" (660)	Window	Black	2	<b>HSQ2426</b>
12	24" (610)	22.6" (574)	36" (914)	Window	Black	2	<b>HSQ2436</b>
12	24" (610)	22.6" (574)	20" (508)	Solid	Black	2	<b>HSQ24S</b>
12	24" (610)	22.6" (574)	26" (660)	Solid	Black	2	<b>HSQ24S26</b>
12	24" (610)	22.6" (574)	36" (914)	Solid	Black	2	<b>HSQ24S36</b>
19	36" (914)	22.6" (574)	20" (508)	Window	Black	4	<b>HSQ36</b>
19	36" (914)	22.6" (574)	26" (660)	Window	Black	4	<b>HSQ3626</b>
19	36" (914)	22.6" (574)	36" (914)	Window	Black	4	<b>HSQ3636</b>
19	36" (914)	22.6" (574)	20" (508)	Solid	Black	4	<b>HSQ36S</b>
19	36" (914)	22.6" (574)	26" (660)	Solid	Black	4	<b>HSQ36S26</b>
19	36" (914)	22.6" (574)	36" (914)	Solid	Black	4	<b>HSQ36S36</b>
26	48" (1219)	22.6" (574)	20" (508)	Window	Black	6	<b>HSQ48</b>
26	48" (1219)	22.6" (574)	26" (660)	Window	Black	6	<b>HSQ4826</b>
26	48" (1219)	22.6" (574)	36" (914)	Window	Black	6	<b>HSQ4836</b>
26	48" (1219)	22.6" (574)	20" (508)	Solid	Black	6	<b>HSQ48S</b>
26	48" (1219)	22.6" (574)	26" (660)	Solid	Black	6	<b>HSQ48S26</b>
26	48" (1219)	22.6" (574)	36" (914)	Solid	Black	6	<b>HSQ48S36</b>

Note: \*For Office White, add "W" to the end of the Catalog No.  
\*\*RWU = Rear Wall Unit.



HSQ48



HSQ36

**Equipment Shelf, Cantilevered**

For use with all QUADCAB® enclosures

Contents: 1 shelf and mounting hardware kit



Description	Dimensions	Color	Catalog. No.
Solid	3.5"H x 17"W x 14"D	Black	<b>MCCCS19</b>
Perforated	3.5"H x 17"W x 14"D	Black	<b>MCCCS19P</b>

**Equipment Shelf, Stationary**

For use with 36" deep QUADCAB® enclosures

Contents: 1 shelf and mounting hardware kit



Description	Dimensions	Color	Catalog. No.
Solid	17.7" W x 29.2" D	Black	<b>CKSSD</b>
Perforated	17.7" W x 29.13" D	Black	<b>MCCPSHLF</b>

**Fan Kit**

Increases ventilation.

Contents: 1 fan tray assembly, (2 fans - 57 CFM each) wired and mounting hardware kit



Description	Catalog No.
114 CFM, 120 VAC, 60 Hz, 36 dBA	<b>HWKF120</b>
114 CFM, 230 VAC, 50 Hz, 36 dBA	<b>HWKF230</b>

**Fan Plate/Fan**

Increases ventilation

Contents: 1 fan, 1 wire guard, 4 lock nuts, screws, and washers and 1 cord with 6' plug



Description	Catalog No.
Blank plate with 4" fan/PVC conduit knock-out	<b>H1KB</b>
Fan, 57 CFM, 120V AC, 60 Hz, 36 dBA	<b>REKEF</b>